




LLC «AUTOMATION-METROLOGY-EXPERT»
Mass-EXPERT — Coriolis mass flow meters
450104, Russia, Ufa, Chernyshevskogo str., 82, office 614
tel./fax: +7 (347) 286-53-50 · e-mail: info@ame-info.ru
web: ame-info.ru



QUESTIONNAIRE

for Mass-EXPERT Coriolis mass flow meter

* — required fields

Send the completed form to info@ame-info.ru

1. GENERAL INFORMATION

Company *		Date	
Contact person *		Phone / fax *	
Address *		E-mail	
Questionnaire No.		Tag number	
		Quantity *	

2. MEASURED MEDIUM

Measured medium *		Phase state *	☐	Description	
Composition (if mixture)		Concentration, % (if solution)		Gas content, % (if liquid)	
Aggressive medium	☐	Fouling tendency	☐	Solids content, %; particle size, mm	

3. PROCESS DATA

Parameter	minimum	nominal	maximum	design	unit of measurement
Flow rate *					☐
Process pressure *					☐
Process temperature *					☐
Allowable pressure drop					☐
Density *					☐
Viscosity *					☐

4. PROCESS CONNECTION

Pipe inner diameter, mm *		Wall thickness, mm		Material *	
Flange standard		Flange facing type		Required DN / PN	
☐				DN	☐
				PN	☐

5. METER DESIGN REQUIREMENTS

Mass flow accuracy (max.) *	☐	Density accuracy (max.)	☐	Certification	☐
Transmitter / sensor mounting	☐	Cable entry type	☐	Power supply	☐
Display	☐	Display interface language	☐	Sensor type	☐
Ambient temperature, °C		from		to	
Output signals					☐

6. ADDITIONAL OPTIONS FROM MASS-EXPERT

Check the options you are interested in — we will include them in your quotation.

☐ Isothermal jacket (option 19S) — maintains constant temperature: bitumen, sulfur, paraffins, fuel oil			
☐ Drop-in replacement of an existing flow meter — same face-to-face length $L_1 = L_2$, no pipe re-welding (incl. direct Endress+Hauser V-type)			
Existing meter (make, model)			Face-to-face length L_1 , mm
☐ Counter flanges with fasteners		Counter flange material	
☐ Conical reducers (if the meter is smaller than the pipe)		☐ 3-A compliant design (food industry)	
☐ Thermal cover		Thermal cover scope	
☐ Ultra-compact transmitter ME400 (stainless steel, non-Ex)			
☐ Pharmaceutical / hygienic design required (surface polishing)			
☐ Spool piece — installed in place of the meter (same face-to-face length)		☐ Cable glands	
☐ On-site installation supervision & commissioning (location and details — specify in Notes)			
☐ Remote support during commissioning			

7. NOTES

The final price and delivery time depend on the options selected; choosing default options keeps both to a minimum.